# DATA SHEET PARLÉ™ TCM-X AVB BEAMTRACKING™ CEILING MICROPHONE

The Parlé™ TCM-X is an AVB low-profile ceiling microphone for use in Tesira® systems. Comprising a network box and a ceiling microphone, each microphone includes Beamtracking™ technology with four 90-degree zones, providing full 360-degree coverage of the meeting space. The TCM-X microphone delivers the same level of performance as our other Beamtracking microphones in a sleek, unobtrusive design that mounts to the ceiling. The TCM-X actively tracks and intelligently mixes conversations from around the table, allowing far-end participants to experience the conversation as they would a face-to-face meeting. Each network box has its own digital signal processing module and comes with an additional RJ-45 connector to add an optional TCM-XEX to the network box. A maximum of two microphones are permitted per network box (one TCM-X or TCM-XA with TCM-XEX). The TCM-X is well suited for a variety of room types and sizes with 10 foot (3 meter) ceilings or lower that require high-quality audio solutions and low profile or unobtrusive microphones.





### **FEATURES**

- Low profile circular ceiling microphone that measures 5.90 inches (150 mm) in diameter
- · Mounts directly to the ceiling to virtually disappear in room
- Beamtracking technology actively tracks and intelligently mixes conversations
- Four 90-degree zones for full 360-degree room coverage
- · Network box includes DSP for Beamtracking
- Single cable connection via category cable
- Beamtracking technology works out-of-box without any lobe aiming or room mapping

- Uses only one channel of AEC per microphone
- LED mute status indicator
- · Available in either black or white
- Evaluated to the requirements of UL 2043 and is suitable for use in air handling spaces
- Additional RJ-45 on network box for connection to a TCM-XEX microphone
- · CE marked, UL listed, and RoHS compliant
- Covered by Biamp Systems' five-year warranty

### **ARCHITECTS & ENGINEERS SPECIFICATIONS**

The Beamtracking™ ceiling microphone shall be designed exclusively for use with Biamp® Tesira® systems. The Beamtracking ceiling microphone shall be comprised of a ceiling mount microphone and a network box. The Beamtracking ceiling microphone shall utilize an AVB/TSN network via an RJ-45 connector for audio networking as well as software configuration and control. The Beamtracking ceiling mount microphone shall contain a sixteen-element digital microphone array, and shall provide four 90-degree zones for 360 degrees of coverage. The Beamtracking ceiling microphone shall offer multidirectional beamforming and automatic signal tracking capabilities. The Beamtracking technology shall operate in conjunction with acoustic echo cancellation technology (AEC) in accordance with U.S. Patent 9659576. The signal processing of the Beamtracking ceiling microphone shall be configurable via the Tesira design software, including but not limited to: signal routing and mixing, equalization, filtering, dynamics, and delay, as well as control, monitoring, and diagnostic tools. The Beamtracking ceiling microphone shall offer simple installation and shall be mountable directly to the ceiling. The Beamtracking ceiling microphone shall be powered by PoE (IEEE 802.3at Class 3, 15.4W). The Beamtracking ceiling microphone shall be suitable for use in air handling spaces in accordance with UL 2043, and shall provide an additional RJ-45 connector to allow connection of one expander TCM-XEX microphone. The Beamtracking ceiling microphone shall be CE marked, UL listed, and compliant with the RoHS directive. Warranty shall be five years. The Beamtracking ceiling microphone shall be Parlé™ TCM-X.

Biamp, Tesira, Parlé, and Beamtracking are either trademarks or registered trademarks of Biamp Systems, LLC in the United States and other countries. Other product names referenced may be trademarks or registered marks of their respective owners and Biamp Systems is not affiliated with or sponsored by these companies.



# PARLÉ TCM-X SPECIFICATIONS

### **CEILING MOUNT MICROPHONE**

16-Element Digital Array Microphone Technology:

Frequency Response (150 Hz - 16 kHz): ± 3dB

Polar Pattern: Active Beamformed

SNR (at 1kHz, 94dBSPL A-Weighted): > 76dB

Maximum SPL (at < 1% THD): 109dB

92dB, A-Weighted Dynamic Range (THD+N < 1%):

> Mute Indicator (Green/Red LED)

**Digital Interface:** Custom/Proprietary

Connector: **RJ-45** 

**Overall Dimensions** 

Height (excluding ceiling mount): 0.6 inches (15 mm) Diameter: 5.90 inches (150 mm) Weight: 0.7 lbs (340 g)

**NETWORK BOX** 

Indicators:

Connectors: Three RJ-45: one between TCM-X

network box and switch, one between the network box and microphone, the other

between TCM-X network box and TCM-XEX

Power: PoE (IEEE 802.3at Class 3, 15.4W)

Indicators: Power Indicator

(Green/Yellow/Red LED)

Digital Interface: Custom/Proprietary

Max Distance Between Devices: 330 feet (100 meters) from

switch to TCM-X network box:

33 feet (10 meters) between TCM-X network box and TCM-XEX

**Overall Dimensions** 

Height: 1.2 inches (30 mm) Width: 6.8 inches (172 mm) Depth: 5.2 inches (132 mm)

Weight: 1.4 lbs (625 g)

**Environmental** 

**Ambient Operating** 

32 - 104° F (0 - 40° C) **Temperature Range:** 

**Humidity:** 0-95% relative humidity (non-condensing)

0-10,000 ft (0-3000m) MSL Altitude:

Compliance:

FCC Part 15B (USA)

CE marked (Europe)

UL and C-UL listed (USA and Canada)

RoHS Directive (Europe)

Evaluated to the requirements

of UL 2043 and is suitable for

use in air handling spaces

# **OPTIONAL ACCESSORIES**



**Seismic Cable Adapter** 

Cable adapter for TCM plenum boxes



**TB-1** 

Tile bridge for TCM plenum boxes



**TCM-X Installation Tool** 


Hole saw and driver



TCM-X-DK

Plenum attachment for drywall ceilings

#### TCM-X Polar Responses at Center of Tracking Zone Patterns Shown at 1000Hz at an elevation of 30° from Ceiling



#### TCM-X Polar Responses at Center of Tracking Zones erns Shown at 2000Hz at an elevation of 30° from Ceiling



## TCM-X Polar Responses at Center of Tracking Zones

